

The Veritas® 6" Traveller makes it straightforward to use the Veritas Plunge Base for Rotary Tools (05J65.01) alongside the Veritas 30" or 52" Power Tool Guides (05J50.12 and 05J50.03, respectively). The traveller increases the speed, accuracy and safety of long cuts made with a rotary tool, such as when routing a groove for narrow stringing or adding fine decorative details with 1/8" shanked molding bits.

Remove the fence arm/guide body assembly from the Veritas Fence and Center Kit (05J65.03), slide the traveller to the approximate position on the fence rods, as shown in **Figure 1**, and tighten the locking knobs. If desired, you can use the optional precision adjuster (05J65.05) to fine-tune the settings. Hook the traveller within the rails on either side of the tool guide.




Figure 1: Setting up the 6" traveller.

The optional UHMW tape may be applied to the traveller to reduce the play between the guide and the traveller, providing smooth operation.

To apply the UHMW tape:

1. Remove the tape backing and stick it to the inner hook of the traveller as illustrated in **Figure 2**. Be sure that it is well adhered.
2. Fold the remaining tape over the hook and push the hook into the mating slot in the guide. Slide the traveller back and forth to ensure that the tape is firmly bonded.
3. Trim off the excess.




Figure 2: Applying the optional UHMW tape. (Traveller body not shown for clarity.)